

# ÖLFLEX® CLASSIC 100 CY 300/500V

가 PVC

ÖLFLEX® CLASSIC 100 CY 300/500V - PVC ,

CPR: [www.lappkabel.com/cpr](http://www.lappkabel.com/cpr)  
EMC-

U<sub>0</sub>/U : 450/750V

ÖLFLEX® CLASSIC 100 CY 450/750V



4kV  
Shielding against electromagnetic fields

EMC-  
( )

(22.02.2024)

# ÖLFLEX® CLASSIC 100 CY 300/500V

: IEC 60332-1-2  
T1

( . 250 /km, 30 MHz )

EN 50525-2-51  
In Anlehnung an EN 50525-2-11

PVC LAPP P8/1 가  
PVC ,  
PVC

ETIM 5: ETIM 5.0 Class-ID: EC001578  
ETIM 5.0 Class 가  
ETIM 6: ETIM 6.0 Class-ID: EC001578  
ETIM 6.0 Class :  
: 5 : VDE 0293-308 T9  
6 : ÖLFLEX® , T7  
: IEC 60228/VDE 0295 class 5  
: : 20 x  
: : 6 x  
: U0/U: 300/500 V  
: 4000 V  
: G = GN/YE  
: X = GN/YE  
: : -5°C ~ +70°C  
: -40°C +80°C

가 가 ( . ) 가  
www.lappkabel.de/en/cable-standradlengths  
: 30 kg or 250 m,  
(e.g. 1 x 500 m or 5 x 100 m ).  
: 4G50 500 m; 4G95 400 m; 4G120 300 m; 4G150 250 m  
가 VAT 가 가



# ÖLFLEX® CLASSIC 100 CY 300/500V

Article number	(CORE) / (mm <sup>2</sup> )	(mm)	(kg/km)	(kg/km)
ÖLFLEX® CLASSIC 100 CY 300/500 V				
0035001	2 X 0.5	7	41	75
0035002	3 G 0.5	7.3	46	83
00350033	4 G 0.5	7.9	55	99
00352013	5 G 0.5	8.4	66	112
0035202	7 G 0.5	8.9	80	132
0035004	2 X 0.75	7.4	46	86
0035005	3 G 0.75	7.9	57	100
00350063	4 G 0.75	8.4	64	115
00350163	5 G 0.75	8.9	77	130
0035203	7 G 0.75	9.7	102	161
0035220	2 X 1.0	7.9	56	98
0035221	3 G 1.0	8.2	65	111
00352223	4 G 1.0	8.7	78	130
00352233	5 G 1.0	9.5	89	153
0035204	7 G 1.0	10.2	113	185
11356500	3 G 1.5	8.9	77	135
11356501	4 G 1.5	9.6	94	165
11356502	3 G 2.5	10.3	118	190
11356503	4 G 2.5	11.3	149	230
11356504	4 G 4.0	13.4	222	345
11356505	4 G 6.0	15.8	317	485
11356506	4 G 10.0	19.5	497	735
11356507	4 G 16.0	22.7	757	1200

(22.02.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02\_03\_16