


AH,

/

Now with UL approval



()

DIN 46228
UL File Nr. E507990,

ETIM 5:

ETIM 5.0 Class-ID: EC000005
ETIM 5.0 class :

ETIM 6:

ETIM 6.0 Class-ID: EC000005
ETIM 6.0 Class :

:

- 55°C +200 °C

:

가

가 VAT 가 가 .

(28.04.2024)

AH,

		mm ²	UL	l1 mm	d1 mm	d2 mm	s mm		/ PU
AH,									
62120200	AH DIN 0,5/6	0.5	yes	6	1	2.1	0.15	PEW 12.090	500
62120210	AH DIN 0,75/6	0.75	yes	6	1.2	2.3	0.15	PEW 12.090	500
61721530	AH DIN 0,75/10	0.75	yes	10	1.2	2.3	0.15	PEW 12.090	500
62120220	AH DIN 1/6	1	yes	6	1.4	2.5	0.15	PEW 12.090	500
61721540	AH DIN 1/10	1	yes	10	1.4	2.5	0.15	PEW 12.090	500
62120230	AH DIN 1,5/7	1.5	yes	7	1.7	2.8	0.15	PEW 12.090	500
61721550	AH DIN 1,5/10	1.5	yes	10	1.7	2.8	0.15	PEW 12.090	500
62120240	AH DIN 2,5/7	2.5	yes	7	2.2	3.4	0.15	PEW 12.090	500
61721560	AH DIN 2,5/12	2.5	yes	12	2.2	3.4	0.15	PEW 12.090	500
62120250	AH DIN 4/9	4	yes	9	2.8	4	0.2	PEW 12.090	500
62120260	AH DIN 6/10	6	yes	10	3.5	4.7	0.2	PEW 12.090	500
62120270	AH DIN 10/12	10	yes	12	4.5	5.8	0.2	PEW 12.091	500
62120280	AH DIN 16/12	16	yes	12	5.8	7.5	0.2	PEW 12.091	500

(28.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16