



ÖLFLEX® CLASSIC 100 SY

가 PVC

ÖLFLEX® CLASSIC 100 SY - PVC , ,

CPR: www.lappkabel.com/cpr
가



: IEC 60332-1-2
, T1

IEC 60227-5 EN 50525-2-51

ÖLFLEX® CLASSIC 100 SY

PVC LAPP P8/1 가

PVC ,
PVC

ETIM 5:

ETIM 5.0 Class-ID: EC001578
ETIM 5.0 Class 가

ETIM 6:

ETIM 6.0 Class-ID: EC001578
ETIM 6.0 Class :

: 5 : VDE 0293-308 T9
6 : ÖLFLEX® , T7

: IEC 60228/VDE 0295 class 5

: : 20 x

: 6 x

: 1.5 mm²: U0/U: 300/500 V

2.5 mm² : U0/U: 450/750 V

2.5 mm² : : U0/U: 600/1000 V

: 4000 V

: G = GN/YE

X = GN/YE

: : -5°C ~ +70°C

: -40°C +80°C

: , 가 가 (.) 가 .
www.lappkabel.de/en/cable-standradlengths

: ≤ 30 kg or ≤ 250 m,

. (e.g. 1 x 500 m or 5 x 100 m).

: ≥ 4G35 500 m; ≥ 4G95 400 m

가 VAT 가 가 .

(27.02.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16

ÖLFLEX® CLASSIC 100 SY

Article number	(CORE) / (mm ²)	(mm)	(kg/km)	(kg/km)
ÖLFLEX® CLASSIC 100 SY; U0/U: 300/500 V				
0016022	2 X 0.75	8.2	14.4	97
0016023	3 G 0.75	8.5	21.6	108
00160243	4 G 0.75	9.2	28.8	126
00160253	5 G 0.75	9.7	36	146
0016027	7 G 0.75	10.3	50	172
0016031	12 G 0.75	12.9	86	260
0016042	2 X 1.0	8.5	19.2	137
0016043	3 G 1.0	8.8	29	154
00160443	4 G 1.0	9.5	38.4	180
00160453	5 G 1.0	10.1	48	202
0016047	7 G 1.0	11	67	242
0016064	2 X 1.5	9.3	29	172
0016065	3 G 1.5	9.7	43	191
00160663	4 G 1.5	10.2	58	217
00160673	5 G 1.5	11.1	72	268
0016069	7 G 1.5	11.9	101	311
0016072	12 G 1.5	15.4	173	499
0016075	18 G 1.5	17.6	259	652
0016077	25 G 1.5	20.3	360	913
ÖLFLEX® CLASSIC 100 SY; U0/U: 450/750 V				
0016087	2 X 2.5	12.1	48	245
0016088	3 G 2.5	12.6	72	278
00160893	4 G 2.5	13.9	96	339
00160903	5 G 2.5	15.2	120	397
0016092	7 G 2.5	16.3	168	470
0016101	2 X 4.0	13.6	76.8	329
00161023	4 G 4.0	15.7	154	457
00161033	5 G 4.0	17.1	192	545
0016106	3 G 6.0	15.8	173	544
00161073	4 G 6.0	17.2	230	687
00161083	5 G 6.0	18.8	288	798
00161103	4 G 10.0	21.3	384	1009



ÖLFLEX® CLASSIC 100 SY

Article number	(CORE) / (mm²)	(mm)	(kg/km)	(kg/km)
00161113	5 G 10.0	23.3	480	1197
00161133	4 G 16.0	24.1	614	1384
00161143	5 G 16.0	26.8	768	1740
00161163	4 G 25.0	29.4	960	2021
00161173	5 G 25.0	32.6	1200	2464
00161183	4 G 35.0	32.4	1344	2570
00161193	5 G 35.0	36	1680	3185
00161203	4 G 50.0	38.8	1920	3514