


ÖLFLEX® CLASSIC PN

Colour-coded PVC control cable for the connection of PROFINET components

ÖLFLEX® CLASSIC PN - flexible PVC cable, colour coded, power cable for PROFINET applications with 24V

PROFINET 24 V power cable
 CPR: www.lappkabel.com/cpr



Colour code according to PROFINET-Guideline "PROFINET Cabling and Interconnection Technology" for clear identification of the cores

4kV

Classified fire behavior according to EU Directive 305/2011 (CPR) with article number selection under www.lappkabel.com/cpr

For power supply of PROFINET components , 가
 WTG() ,
 PVC outer sheath is resistant to acids and alkalis

: IEC 60332-1-2 , T1

ÖLFLEX® CLASSIC PN

EN 50525-2-51
In Anlehnung an EN 50525-2-11

PVC LAPP P8/1 가
(RAL 7001) PVC

ETIM 5: ETIM 5.0 Class-ID: EC001578
ETIM 5.0 Class 가

ETIM 6: ETIM 6.0 Class-ID: EC001578
ETIM 6.0 Class :

: brown (L1), blue (N1),
4/5 cores: additionally black (L2), white (N2)
3/5 cores: additionally pink (FE)

: IEC 60228/VDE 0295 class 5

WTG : TW-0 & TW-1, T0

: : 15 x
: 4 x

: U0/U: 300/500 V

: 4000 V

: : -5°C ~ +70°C

: -40°C +80°C

: , 가 가 . (.) 가 .
www.lappkabel.de/en/cable-standradlengths
: 30 kg or 250 m,

. (e.g. 1 x 500 m or 5 x 100 m).

: 5G50 500 m; 5G95 400; 3G120 500 m; 4G120 300; 4G185 250 m

가 VAT 가 가 .

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16



ÖLFLEX® CLASSIC PN

Article number	(CORE) / (mm ²)	(mm)	(kg/km)	(kg/km)
1120831	3 X 0.75	5.7	21.6	55
1120838	4 X 0.75	6.2	28.8	66
1120832	5 X 0.75	6.7	36	79
1120833	3 X 1.5	6.7	43.2	84
1120839	4 X 1.5	7.2	57.6	104
1120834	5 X 1.5	8.1	72	128
1120835	3 X 2.5	8.1	72	132
1120837	4 X 2.5	8.9	96	163
1120836	5 X 2.5	10.0	120	200

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16