

DIN-Coil

/



Lapp



End sleeves on coil for maximum simplification and time saving.
 Ideally suited for automated cable assembly in large quantities.
 Particularly easy to combine with GLW automatic crimping machines.
 UL certification according to technical data enables use of the product in the North American region.

DIN , , DIN 46228, 4
 3000 가
 To get a (partially) automated crimp connection by means of an automatic crimping machine.

: 25 cm

ETIM 5: ETIM 5.0 Class-ID: EC000005
 ETIM 5.0 class :

ETIM 6: ETIM 6.0 Class-ID: EC000005
 ETIM 6.0 Class :

DIN-Coil

: /PP
:
: -5°C 105°C,
120°C
, (:) 가
,
가 VAT 가 가 .



DIN-Coil

		mm ²		l1 mm	l2 mm	d1 mm	d2 mm	R mm	()
61802052	DIN coil 0.5	0.5		14.5	8	1.1	2.6	3.5	3000 x 1
61802054	DIN coil 0.75	0.75		14.5	8	1.3	2.8	3.6	3000 x 1
61802056	DIN coil 1.0	1		14.5	8	1.5	3	3.9	3000 x 1
61802058	DIN coil 1.5	1.5		14.5	8	1.8	3.4	4.2	2500 x 1
61802060	DIN coil 2.5	2.5		14.5	8	2.3	4.2	5	1500 x 1
61802053	-	0.5		14.5	8	1.1	2.6	3.5	-
61802055	-	0.75		14.5	8	1.3	2.8	3.6	-
61802057	-	1.0		14.5	8	1.5	3	3.9	-
61802059	-	1.5		14.5	8	1.8	3.4	4.2	-

(24.04.2024)


©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16

DIN-Coil



(24.04.2024)

©2024 Lapp Group - all rights reserved.
<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16