


M / F

M/Type F,



가



가

ETIM 5:

ETIM 5.0 Class-ID: EC000516  
ETIM 5.0 class : /

ETIM 6:

ETIM 6.0 Class-ID: EC000516  
ETIM 6.0 Class : /

:

max. +105°C

:

가 VAT 가 가 .

(25.04.2024)

		UL	/	W (mm)	(mm)	(mm)	/ PU
( M)							
63300100	408-2 M	no	2	15.3	13.2	32.2	100
63300110	408-4 M	no	4	27.5	16.8	32.6	100
63300120	408-6 M	no	6	31.2	18.8	32.9	100
63300130	408-8 M	no	8	40.4	18.8	33.1	100
- ( F)							
63300140	408-2 F	no	2	12.6	10	23.2	100
63300150	408-4 F	no	4	24.5	14.1	24	100
63300160	408-6 F	no	6	28.2	14.9	24.3	100
63300170	408-8 F	no	8	37.4	15.4	24.4	100

(25.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02\_03.16