



ÖLFLEX® DC 100

ÖLFLEX® DC 100 - 0.75/1.5 kV DC

DC , EN 60445



Specially constructed for the long term operation with DC voltage of max. 0,9 / 1,8 kV operating voltage
DC

가 , 가

: IEC 60332-1-2
ISO 4892-2UV UV
EN 50396

ÖLFLEX® DC 100

가
 : PVC
 : (L+), (L-), -
 PVC , (RAL 9005)

ETIM 5: ETIM 5.0 Class-ID: EC000057
 ETIM 5.0
 ETIM 6: ETIM 6.0 Class-ID: EC000057
 ETIM 6.0 Class :
 : , , -
 : IEC 60228/VDE 0295 class 5
 : : 15 x
 : : 4 x
 : DC(-): 0.75 kV DC(-): 1.5 kV
 : 4000 V
 : G = GN/YE
 : X = GN/YE
 : : -5°C ~ +70°C
 : : -40°C +80°C

가 가 (.) 가 .
 www.lappkabel.de/en/cable-standradlengths
 : 30 kg or 250 m,
 . (e.g. 1 x 500 m or 5 x 100 m).
 가 VAT 가 가 .



ÖLFLEX® DC 100

Article number	(CORE) / (mm ²)	(mm)	(kg/km)	(kg/km)
11101106	3 G 1.5	8.7	43	134.2
11101107	3 G 2.5	10.0	72	188.2
11101108	3 G 4.0	11.4	115	263.4
11101109	3 G 6.0	12.6	173	346.2
11101111	3 G 16.0	18.3	461	823.8
11101113	3 G 25.0	23.0	720	1071
11101114	3 G 35.0	25.6	1008	1684

(07.05.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16