

Tube cable lugs Cu

Tube cable lug made of copper, heat-resistant up to +180°C, for use with ÖLFLEX® HEAT cables/single cores, available in different dimensions.



Withstand temperatures up to +180°C.

Compatible with equally heat-resistant ÖLFLEX® HEAT cables/single cores (e.g. ÖLFLEX® HEAT 180 product series).

Heat resistance tested in 1000 test cycles with ÖLFLEX® HEAT 180 cables, in accordance with DIN EN IEC 61238-1-1.

Suitable for use with KLAUKE crimping tools.

UL certification according to technical data enables the product to be used in the North American market.

For creating a safe crimp connection with multi-wire and fine-wire round cables in classes 2 and 5 in accordance with DIN EN 60228.

(13.05.2024)

Tube cable lugs Cu

UL-Zertifizierungen sind dem Datenblatt zu entnehmen

ETIM 5:

ETIM 5.0 Class-ID: EC001051

ETIM 5.0 class :

:

:

up to +180°C

*

,

가

VAT

가

가

.

(13.05.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16

Tube cable lugs Cu

	UL	(mm)	d mm	W mm
63207053	yes	15.25	1.3	6
63207054	yes	17	1.3	6.5
63207055	yes	18.75	1.3	7.5
63207056	yes	15.25	1.8	6.5
63207057	yes	17	1.8	6.5
63207058	yes	18.75	1.8	7.5
63207059	yes	22.5	1.8	9
63207061	yes	15.25	2.3	7.5
63207062	yes	17	2.3	7.5
63207063	yes	18.75	2.3	8.5
63207064	yes	22.5	2.3	9.5
63207065	yes	27.75	2.3	13
63207066	yes	21.75	3	8.5
63207067	yes	21.75	3	9
63207068	yes	25.5	3	10
63207069	yes	30.5	3	13
63207071	yes	23	4	9.5
63207072	yes	25	4	9.5
63207073	yes	26	4	10
63207074	yes	30.5	4	14
63207075	yes	28.5	4.5	12
63207076	yes	28.5	4.5	12
63207077	yes	35	4.5	15
63207078	yes	39	4.5	17
63207079	yes	42	4.5	19
63207080	yes	31.5	5.5	12
63207081	yes	33.25	5.5	12
63207082	yes	37.5	5.5	15
63207083	yes	41.5	5.5	17
63207084	yes	45	5.5	19

(13.05.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16