



ÖLFLEX® CLASSIC 110 LT

PVC

ÖLFLEX® CLASSIC 110 LT - YY , , , 300/500V PVC , YSLY

CPR: www.lappkabel.com/cpr
ISO 4892-2UV UV



4kV

WTG()

(23.04.2024)

ÖLFLEX® CLASSIC 110 LT

: IEC 60332-1-2
-30°C
ISO 4892-2UV UV
EN 50396

EN 50525-2-51

가
: PVC,

: PVC, ,

ETIM 5:

ETIM 5.0 Class-ID: EC000104
ETIM 5.0

ETIM 6:

ETIM 6.0 Class-ID: EC000104
ETIM 6.0 Class :

:

Black with white numbers acc. to VDE 0293-334

:

IEC 60228/VDE 0295 class 5

WTG

:

TW-0 & TW-2, T0

:

: 15 x

: 4 x

:

U0/U: 300/500 V

:

4000 V

:

G = GN/YE

X = GN/YE

:

: -30 °C ~ +70 °C

: -40°C +80°C

가 가 (.) 가 .
: www.lappkabel.de/en/cable-standradlengths
30 kg or 250 m,
(e.g. 1 x 500 m or 5 x 100 m).

가 VAT 가 가 .

(23.04.2024)

ÖLFLEX® CLASSIC 110 LT

Article number	(CORE) / (mm ²)	(mm)	(kg/km)	(kg/km)
1120730	2 X 0.75	5.4	14.4	45
1120731	3 X 0.75	5.7	21.6	55
1120732	3 G 0.75	5.7	21.6	55
1120733	4 X 0.75	6.2	28.8	66
1120734	4 G 0.75	6.2	28.8	66
1120735	5 G 0.75	6.7	36	79
1120736	7 G 0.75	7.3	50.4	101
1120737	12 G 0.75	9.9	86.4	171
1120738	18 G 0.75	11.7	130	244
1120739	25 G 0.75	13.8	180	337
1120740	2 X 1.0	5.7	19.2	53
1120741	3 X 1.0	6	28.8	65
1120742	3 G 1.0	6	28.8	65
1120743	4 X 1.0	6.5	38.4	79
1120744	4 G 1.0	6.5	38.4	79
1120745	5 G 1.0	7.1	48	94
1120746	7 G 1.0	8	67.2	126
1120747	12 G 1.0	10.5	115	205
1120748	18 G 1.0	12.7	173	300
1120749	25 G 1.0	14.7	240	408
1120750	2 X 1.5	6.3	29	68
1120751	3 X 1.5	6.7	43	84
1120752	3 G 1.5	6.7	43	84
1120753	4 X 1.5	7.2	58	104
1120754	4 G 1.5	7.2	58	104
1120755	5 X 1.5	8.1	72	128
1120756	5 G 1.5	8.1	72	128
1120757	7 X 1.5	8.9	101	166
1120758	7 G 1.5	8.9	101	166
1120759	12 G 1.5	12	173	279
1120760	18 G 1.5	14.4	259	407
1120761	25 G 1.5	16.9	360	560
1120762	2 X 2.5	7.5	48	101
1120763	3 G 2.5	8.1	72	132

(23.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16



ÖLFLEX® CLASSIC 110 LT

Article number	(CORE) / (mm ²)	(mm)	(kg/km)	(kg/km)
1120764	4 G 2.5	8.9	96	163
1120765	5 G 2.5	10	120	200
1120766	7 G 2.5	11.1	168	267
1120767	12 G 2.5	14.8	288	445
1120768	18 G 2.5	17.8	432	648
1120769	25 G 2.5	20.8	600	890
1120770	4 G 4.0	10.8	154	249
1120771	5 G 4.0	12.1	192	305
1120772	4 G 6.0	13	230	365
1120773	5 G 6.0	14.5	288	447

(23.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16