



# ÖLFLEX® CLASSIC 115 CY BK

PVC

ÖLFLEX® CLASSIC 115 CY BK - PVC  
가 , 300/500V

가 가

가 ,  
EMC-



WTG( )

(24.04.2024)



# ÖLFLEX® CLASSIC 115 CY BK

ISO 4892-2UV UV  
: IEC 60332-1-2  
, T1

( . 250 /km, 30 MHz )

EN 50525-2-51

PVC LAPP P8/1 가

PVC ,

ETIM 5:

ETIM 5.0 Class-ID: EC000104  
ETIM 5.0

ETIM 6:

ETIM 6.0 Class-ID: EC000104  
ETIM 6.0 Class :

:

Black with white numbers acc. to VDE 0293-334

:

IEC 60228/VDE 0295 class 5

WTG :

TW-0 & TW-1, T0

:

: 20 x

: 6 x

:

U0/U: 300/500 V

:

Core/core: 4000 V

Core/screen: 2000 V

:

G = GN/YE

X = GN/YE

:

: -5°C ~ +70°C

: -40°C +80°C

가 가 ( . ) 가  
www.lappkabel.de/en/cable-standradlengths  
: 30 kg or 250 m,  
(e.g. 1 x 500 m or 5 x 100 m ).

가 VAT 가 가 .

(24.04.2024)

ÖLFLEX® CLASSIC 115 CY BK

| Article number | (CORE) / (mm <sup>2</sup> ) | (mm) | (kg/km) | (kg/km) |
|----------------|-----------------------------|------|---------|---------|
| 1136510        | 2 X 0.5                     | 5.8  | 36      | 54      |
| 1136511        | 3 G 0.5                     | 6.1  | 43      | 63      |
| 1136512        | 3 X 0.5                     | 6.1  | 43      | 63      |
| 1136513        | 4 G 0.5                     | 6.5  | 49      | 71      |
| 1136514        | 4 X 0.5                     | 6.5  | 49      | 71      |
| 1136515        | 5 G 0.5                     | 7    | 57      | 86      |
| 1136516        | 5 X 0.5                     | 7    | 57      | 86      |
| 1136517        | 7 G 0.5                     | 7.5  | 69      | 105     |
| 1136518        | 7 X 0.5                     | 7.5  | 69      | 105     |
| 1136519        | 12 G 0.5                    | 9.9  | 104     | 163     |
| 1136520        | 12 X 0.5                    | 9.9  | 104     | 163     |
| 1136521        | 18 G 0.5                    | 11.5 | 141     | 226     |
| 1136522        | 25 G 0.5                    | 13.4 | 211     | 350     |
| 1136523        | 2 X 0.75                    | 6.2  | 43      | 59      |
| 1136110        | 3 G 0.75                    | 6.5  | 52      | 76      |
| 1136525        | 3 X 0.75                    | 6.5  | 52      | 76      |
| 1136111        | 4 G 0.75                    | 7    | 61      | 91      |
| 1136527        | 4 X 0.75                    | 7    | 61      | 91      |
| 1136113        | 5 G 0.75                    | 7.7  | 72      | 100     |
| 1136529        | 5 X 0.75                    | 7.7  | 72      | 100     |
| 1136114        | 7 G 0.75                    | 8.3  | 89      | 127     |
| 1136531        | 7 X 0.75                    | 8.3  | 89      | 127     |
| 1136115        | 12 G 0.75                   | 10.9 | 138     | 232     |
| 1136533        | 18 G 0.75                   | 12.7 | 211     | 292     |
| 1136534        | 25 G 0.75                   | 14.8 | 280     | 435     |
| 1136535        | 2 X 1.0                     | 6.5  | 51      | 71      |
| 1136536        | 3 G 1.0                     | 6.8  | 62      | 86      |
| 1136537        | 3 X 1.0                     | 6.8  | 62      | 86      |
| 1136538        | 4 G 1.0                     | 7.3  | 74      | 98      |
| 1136539        | 4 X 1.0                     | 7.3  | 74      | 98      |
| 1136540        | 5 G 1.0                     | 8.1  | 88      | 121     |
| 1136541        | 5 X 1.0                     | 8.1  | 88      | 121     |
| 1136542        | 7 G 1.0                     | 8.8  | 112     | 147     |
| 1136543        | 7 X 1.0                     | 8.8  | 112     | 147     |

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02\_03.16

ÖLFLEX® CLASSIC 115 CY BK

| Article number | (CORE) / (mm <sup>2</sup> ) | (mm) | (kg/km) | (kg/km) |
|----------------|-----------------------------|------|---------|---------|
| 1136544        | 12 G 1.0                    | 11.5 | 185     | 249     |
| 1136545        | 18 G 1.0                    | 13.9 | 268     | 364     |
| 1136546        | 25 G 1.0                    | 15.9 | 354     | 486     |
| 1136547        | 2 X 1.5                     | 7.1  | 65      | 86      |
| 1136548        | 3 G 1.5                     | 7.5  | 82      | 112     |
| 1136549        | 3 X 1.5                     | 7.5  | 82      | 112     |
| 1136550        | 4 G 1.5                     | 8.2  | 100     | 135     |
| 1136551        | 4 X 1.5                     | 8.2  | 100     | 135     |
| 1136552        | 5 G 1.5                     | 8.9  | 119     | 148     |
| 1136553        | 5 X 1.5                     | 8.9  | 119     | 148     |
| 1136554        | 7 G 1.5                     | 9.9  | 154     | 192     |
| 1136555        | 7 X 1.5                     | 9.9  | 154     | 192     |
| 1136556        | 12 G 1.5                    | 13   | 268     | 332     |
| 1136557        | 18 G 1.5                    | 15.6 | 373     | 484     |
| 1136558        | 25 G 1.5                    | 17.9 | 530     | 734     |
| 1136559        | 34 G 1.5                    | 20.8 | 683     | 944     |
| 1136560        | 3 G 2.5                     | 8.9  | 118     | 151     |
| 1136561        | 4 G 2.5                     | 9.9  | 147     | 188     |
| 1136562        | 5 G 2.5                     | 11   | 176     | 224     |
| 1136563        | 7 G 2.5                     | 11.9 | 253     | 294     |
| 1136564        | 12 G 2.5                    | 16   | 355     | 521     |
| 1136565        | 18 G 2.5                    | 19   | 569     | 740     |
| 1136566        | 4 G 4.0                     | 11.6 | 248     | 287     |
| 1136567        | 4 G 6.0                     | 14.2 | 343     | 424     |
| 1136568        | 4 G 10.0                    | 17.2 | 495     | 637     |
| 1136569        | 5 G 10.0                    | 19.5 | 592     | 824     |
| 1136570        | 4 G 16.0                    | 20.2 | 800     | 1050    |
| 1136571        | 5 G 16.0                    | 22.6 | 895     | 1285    |
| 1136572        | 4 G 25.0                    | 25.1 | 1075    | 1413    |
| 1136573        | 4 G 35.0                    | 28   | 1576    | 1867    |

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02\_03\_16