

SILVYN® AS

SILVYN®SILVYN® AS



VDE
DIN 49012, DIN EN IEC 61386-23 G
VDE 0165 DIN EN 50281-1-2 EX-area

(23.12.2023)



SILVYN® AS

PU = 10m()

ETIM 5:

ETIM 5.0 Class-ID: EC001179

ETIM 5.0 class :

ETIM 6:

ETIM 6.0 Class-ID: EC001179

ETIM 6.0 Class :

:

IEC EN 61386-23

:

:

+220°C

가 VAT 가 가 .

(23.12.2023)

©2023 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16



SILVYN® AS

	()	ID x OD mm	(mm)	SILVYN® MSK-M	SILVYN® US-M	SILVYN® US	PU ring (m)
SILVYN® AS							
61802080	10	8 x 10	28	12 x 1,5	10 x 1,0	7	50
61802090	14	11 x 14	34	16 x 1,5	12 x 1,5	9	50
61802100	17	14 x 17	40	20 x 1,5	16 x 1,5	11	50
61802110	19	16 x 19	45	-	-	13,5	50
61802120	21	18 x 21	50	25 x 1,5	20 x 1,5	16	50
61802130	27	23 x 27	63	32 x 1,5	25 x 1,5	21	50
61802140	36	31 x 36	85	40 x 1,5	32 x 1,5	29	25
61802150	45	40 x 45	100	50 x 1,5	40 x 1,5	36	25
61802170	56	51 x 56	125	63 x 1,5	50 x 1,5	48	25

(23.12.2023)

©2023 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16