

SILVYN® EDU-AS

SILVYN® EDU-AS

가



(08.05.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16



SILVYN® EDU-AS

VDE
DIN 49012, DIN EN IEC 61386-23 K
VDE 0165 DIN EN 50281-1-2 EX-area

PU = 10m()

ETIM 5:

ETIM 5.0 Class-ID: EC001179

ETIM 5.0 class :

ETIM 6:

ETIM 6.0 Class-ID: EC001179

ETIM 6.0 Class :

:

IEC EN 61386-23

:

:

:

+220°C

가 VAT 가 가 .

(08.05.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16



SILVYN® EDU-AS

	()	ID x OD mm	(mm)	SILVYN® MSK-M	SILVYN® US-M	SILVYN® US	PU ring (m)
SILVYN® EDU-AS							
61802380	10	7 x 10	28	12 x 1,5	10 x 1,0	7	50
61802390	14	10 x 14	34	16 x 1,5	12 x 1,5	9	50
61802400	17	13 x 17	40	20 x 1,5	16 x 1,5	11	50
61802410	19	15 x 19	45	-	-	13,5	50
61802420	21	17 x 21	50	25 x 1,5	20 x 1,5	16	50
61802430	27	22 x 27	63	32 x 1,5	25 x 1,5	21	50
61802440	36	29 x 36	85	40 x 1,5	32 x 1,5	29	25
61802450	45	38 x 45	100	50 x 1,5	40 x 1,5	36	25
61802470	56	49 x 56	135	63 x 1,5	50 x 1,5	48	25