

SILVYN® FPAD-M

Conduit fitting with Integrated cable strain relief for use with protective conduits SILVYN® FPAS and SILVYN® HCC

SKINTOP®



CE UK
CA



SKINTOP®



Provides additional strain relief for cable(s) through integrated SKINTOP® cable gland with flexible lamellas.

Quick-release fastener with locking device protects against unintentional opening of the conduit system.

Simple disassembly of the conduit fitting by help of a screwdriver.

Liquid-tight in accordance with protection class IP 66 / IP 68 (on the hose side, in conjunction with SILVYN® FPAS and

(21.02.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16

SILVYN® FPAD-M

SILVYN® HCC protective conduits).

Large, variable clamping ranges allow for different cable outer diameters.

For universal use at machine interfaces to connect a protective conduit system.

For protective conduit systems that require additional strain relief while maintaining a high level of sealing.

For use with SILVYN® FPAS and SILVYN® HCC protective conduits.

Can be used in dry, wet and especially in rough and oily environments.

Withstands chemical and mechanical stress.

UV

Conduit fitting is openable with a screwdriver

가
SKINTOP®

ETIM 5:

ETIM 5.0 Class-ID: EC001176

ETIM 5.0 Class :

ETIM 6:

ETIM 6.0 Class-ID: EC001176

ETIM 6.0 Class :

:

IEC EN 61386-23

:

(RAL 9005), UV

:

PA66

가:

IP66 or IP68 depending on the fitting

:

-30°C ~ +100°C

가 VAT 가 가 .

(21.02.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16



SILVYN® FPAD-M

		Clamping range in mm	(thread) (mm)	SILVYN® FPAS	SILVYN® HCC	/ PU
SILVYN® FPAD-M IP66						
61805112	16 x 1.5	4.0 - 10.0	8	16	16	10
61805113	20 x 1.5	6.0 - 13.0	9	20	20	10
61805114	25 x 1.5	8.0 - 17.0	10	25	25	10
SILVYN® FPAD-M IP68						
61805109	16 x 1.5	4.0 - 10.0	8	16	16	10
61805110	20 x 1.5	6.0 - 13.0	9	21	-	10
61805111	25 x 1.5	8.0 - 17.0	10	28	-	10