

# FIPLOCK® ONE MS-PG

FIPLOCK® PA6 / PA12

FIPLOCK<sup>®</sup> ONE MS-PG



(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02\_03.16

# FIPLOCK® ONE MS-PG



IP

FIPLOCK®  
PA6 / PA12  
가

360°

ETIM 5:	ETIM 5.0 Class-ID: EC001176
	ETIM 5.0 Class :
ETIM 6:	ETIM 6.0 Class-ID: EC001176
	ETIM 6.0 Class :
:	IEC EN 61386-23
	EN 45545-2 HL3
:	(RAL 7005) (RAL 9005), UV
:	PA 6
	UL 94V-0
가:	IP66/IP67/IP68/IP69
:	-45°C ~ +120°C

(24.04.2024)



## FIPLOCK® ONE MS-PG

가 VAT 가 가 .

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02\_03.16



# FIPLOCK® ONE MS-PG

	PG	Clamping range in mm	SW 1/2 mm	(thread) (mm)	FIPLOCK® PA6 / PA12		/ PU
61804921	9	4.0 - 8.0	17.0 / 20.0	6	10		10
61804922	11	4.0 - 10.0	20.0 / 20.0	6	10		10
61804923	11	4.0 - 10.0	20.0 / 22.0	6	12		10
61804924	13.5	5.0 - 12.0	22.0 / 22.0	6.5	12		10
61804925	16	8.0 - 14.0	24.0 / 27.0	6.5	17		10
61804926	21	11.0 - 18.0	30.0 / 36.0	7	23		6
61804927	29	16.0 - 25.0	40.0 / 41.0	8	29		6
61804928	36	19.0 - 32.0	50.0 / 52.0	15	36		4
61804929	48	34.0 - 44.0	64.0 / 65.0	15	48		4

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02\_03.16