

# FIPLOCK® ONE ST-M

FIPLOCK® PA6 / PA12

FIPLOCK<sup>®</sup> ONE ST-M

SKINTOP®



**CE UK CA**



(23.12.2023)

# FIPLOCK® ONE ST-M



IP

FIPLOCK®  
PA6 / PA12  
가

360°

ETIM 5:

ETIM 5.0 Class-ID: EC001176

ETIM 5.0 Class :

ETIM 6:

ETIM 6.0 Class-ID: EC001176

ETIM 6.0 Class :

:

IEC EN 61386-23

EN 45545-2 HL3

:

(RAL 7005)

(RAL 9005), UV

:

PA 6

가:

UL 94V-0

IP66/IP67/IP68/IP69

(23.12.2023)

©2023 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02\_03.16



# FIPLOCK® ONE ST-M

:

-45°C ~ +120°C

가 VAT 가 가 .

(23.12.2023)

FIPLOCK® ONE ST-M

		Clamping range in mm	SW 1/2 mm	(thread) (mm)	FIPLOCK® PA6 / PA12	/ PU
61804807	16 x 1.5	3.5 - 7.0	19.0 / 20.0	8	10	10
61804808	16 x 1.5	3.5 - 7.0	19.0 / 22.0	8	12	10
61804809	20 x 1.5	4.0 - 10.0	25.0 / 22.0	9	12	10
61804811	20 x 1.5	4.0 - 10.0	25.0 / 27.0	9	17	10
61804812	25 x 1.5	5.0 - 13.0	30.0 / 27.0	10	17	10
61804813	25 x 1.5	5.0 - 13.0	30.0 / 36.0	10	23	6
61804814	32 x 1.5	6.0 - 15.0	36.0 / 36.0	10	23	6
61804815	32 x 1.5	6.0 - 15.0	36.0 / 41.0	10	29	6
61804816	40 x 1.5	9.0 - 23.0	46.0 / 41.0	10	29	6
61804817	40 x 1.5	9.0 - 23.0	46.0 / 52.0	10	36	4
61804818	50 x 1.5	24.0 - 29.0	55.0 / 52.0	12	36	4
61804819	50 x 1.5	24.0 - 29.0	55.0 / 65.0	12	48	4
61804821	63 x 1.5	28.0 - 39.0	66.0 / 65.0	12	48	4
61804822	16 x 1.5	3.5 - 7.0	19.0 / 20.0	8	10	10
61804823	16 x 1.5	3.5 - 7.0	19.0 / 22.0	8	12	10
61804824	20 x 1.5	4.0 - 10.0	25.0 / 22.0	9	12	10
61804825	20 x 1.5	4.0 - 10.0	25.0 / 27.0	9	17	10
61804826	25 x 1.5	5.0 - 13.0	30.0 / 27.0	10	17	10
61804827	25 x 1.5	5.0 - 13.0	30.0 / 36.0	10	23	6
61804828	32 x 1.5	6.0 - 15.0	36.0 / 36.0	10	23	6
61804829	32 x 1.5	6.0 - 15.0	36.0 / 41.0	10	29	6
61804831	40 x 1.5	9.0 - 23.0	46.0 / 41.0	10	29	6
61804832	40 x 1.5	9.0 - 23.0	46.0 / 52.0	10	36	4
61804833	50 x 1.5	24.0 - 29.0	55.0 / 52.0	12	36	4
61804834	50 x 1.5	24.0 - 29.0	55.0 / 65.0	12	48	4
61804835	63 x 1.5	28.0 - 39.0	66.0 / 65.0	12	48	4

(23.12.2023)

©2023 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02\_03.16