



SILVYN® SP

SILVYN® SP - PVC



SILVYN® SSV/SSV-M + SCH
IP 54



SILVYN®
SSVZ/SSVZ-M + SCH
IP 54



SILVYN®
USK/USK-M
IP 54



SILVYN® SCH



가

가

PVC
PVC

ETIM 5:

ETIM 5.0 Class-ID: EC001177

ETIM 5.0 Class :

ETIM 6:

ETIM 6.0 Class-ID: EC001177

ETIM 6.0 Class :

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16



SILVYN® SP

:

:

:

:

IEC EN 61386-23

(RAL 7001)

PVC

-15 °C

+60 °C

PVC, SBR/NBR

가 VAT 가 가 .

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16



SILVYN® SP

	ID x OD mm	(mm)	SILVYN® SSV-M/SSVZ-M	SILVYN® USK-M	SILVYN® SSV/SSVZ	SILVYN® USK	SILVYN® SCH	PU ring (m)
SILVYN® SP								
61714000	10.0 x 14.0	50	16 x 1,5/1	12 x 1,5	9/1	9	10 - 16 S	25
61714010	12.0 x 16.0	60	16 x 1,5/2	16 x 1,5	9/2	11	12 - 20 S	25
61714020	14.0 x 18.0	70	20 x 1,5/1	-	11/1	13,5	12 - 20 S	25
61714100	16.0 x 20.0	70	20 x 1,5/2	20 x 1,5	11/2	16	16 - 25 S	25
61714110	22.0 x 27.0	90	25 x 1,5	25 x 1,5	16	21	20 - 32 S	25
61714120	30.0 x 36.0	140	32 x 1,5	32 x 1,5	29/1	29	25 - 40 S	25
61714070	38.0 x 44.0	190	40 x 1,5	40 x 1,5	36	36	32 - 50 S	25
61714080	45.0 x 51.0	240	50 x 1,5	-	42	-	40 - 60 S	25
61714090	49.0 x 56.0	250	63 x 1,5	50 x 1,5	48	48	40 - 60 S	25