

# SILVYN® HIPROJACKET

+1640°C

SILVYN® HIPROJACKET      +1640°C

Hazard Level: HL 3



30%  
SILVYN® HIPROSILTAPE

IP67      가

, , ,      가 ,  
/

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02\_03.16

# SILVYN® HIPROJACKET

The manufacturing process of silicone may result in small air bubbles and openings in the outer sheath, which do not affect the product properties.

ETIM 5:	ETIM 5.0 Class-ID: EC002254	
	ETIM 5.0	:
ETIM 6:	ETIM 6.0 Class-ID: EC002254	
	ETIM 6.0 Class	:
:	EN 45545-2 HL1 / HL2 / HL3	
	NF F 16-101 I2/F1	
	NF EN ISO 11925-2	
	DIN 5510-2 S4/SR2/ST2	
	SAE AS 1072 Type 2	
:	30m VPE	
:		
:		LOI 42.5
가:	SILVYN® HIPROJACKET AMG	IP 54
	SILVYN® HIPROSILTAPE	IP 67
:	-40 °C	+260 °C
	+800°C for approx. 20 min (flame treatment)	
	+800°C for approx. 20 min (radiation heat)	
	+1640°C for approx. 15-30 sec (liquid-metal contact)	

가 VAT 가 가 .

(24.04.2024)



SILVYN® HIPROJACKET

	( )	ID x OD mm		SILVYN® HIPROJACKET Insert set	PU ring (m)
SILVYN® HIPROJACKET					
52021385	6	6.0 x 15.0	-	-	15
61713003	10	10.0 x 15.0	-	-	15
61713005	13	13.0 x 18.0	M16 / PG 11 / NPT 1/2"	13	15
61713007	16	16.0 x 22.0	M20 / PG 16 / NPT 1/2"	16	15
61713010	19	19.0 x 25.0	-	-	15
61713011	22	22.0 x 28.0	M25 / PG 21 / NPT 3/4"	22	15
61713000	25	25.0 x 31.0	M32 / PG 29 / NPT 1"	25	15
61713014	29	29.0 x 35.0	-	-	15
61713015	32	32.0 x 38.0	-	-	15
61713016	35	35.0 x 41.0	M40 / PG 36 / NPT 1-1/4"	35	15
61713017	38	38.0 x 44.0	M50 / PG 42 / NPT 1-1/2"	38	15
61713018	41	41.0 x 47.0	-	-	15
61713021	44	44.0 x 50.0	-	-	15
61713019	51	51.0 x 57.0	M63 / PG 48 / NPT 2"	51	15
61713022	57	57.0 x 63.0	-	-	15
61713025	64	64.0 x 70.0	-	-	15
61713027	70	70.0 x 76.0	-	-	15
61713028	76	76.0 x 82.0	-	-	15
61713029	83	83.0 x 89.0	-	-	15
61713037	89	89.0 x 95.0	-	-	15
61713038	95	95.0 x 101.0	-	-	15
61713039	102	102.0 x 108.0	-	-	15

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02\_03.16