

## Cable ties with steel nose with labelling area

가 TY-RAP®

TY 53 M / TY 532 M



TY 51 M



가

가

가

: E49405,  
UL94 V-2

TY 51 M:  
TY 53 M/TY 532 M:

ETIM 5:

ETIM 5.0 Class-ID: EC000046

ETIM 5.0 :

ETIM 6:

ETIM 6.0 Class-ID: EC000046

ETIM 6.0 Class :

:

:

6.6

:

-40°C

+85°C

(23.12.2023)



## Cable ties with steel nose with labelling area

TY-RAP® Thomas & Betts

가

가 VAT 가 가 .

(23.12.2023)

Cable ties with steel nose with labelling area

	Article description	UL	x (mm)	Bundling Ø (mm)	(mm)	(N)	/ PU
61716020	TY 51 M	yes	92.0 x 2.4	10 - 16	25 x 8	80	500
61715840	TY 46 MD	yes	184.0 x 4.8	9.5 - 45	30 x 24	220.0	500
61715880	TY 46 MT	yes	184.0 x 4.8	9.5 - 45	46 x 24	220.0 3	500
61715920	TY 46 MF	yes	184.0 x 4.8	9.5 - 45	63 x 24	220.0	250
61715780	TY 546 M	yes	184.0 x 4.8	9.5 - 45	13 x 24	220	100
61715950	TY 548 M	yes	360.0 x 4.8	19 - 102	13 x 54	220	100
61716080	TY 53 M	yes	102.0 x 2.4	2 - 16	21 x 9	80	500
61716560	TY 532 M	yes	212.0 x 2.4	2 - 51	21 x 9	80	1000

(23.12.2023)

©2023 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02\_03.16