

# DKK double clamp

DKK



ÖLFLEX® 가 -LIFT RH RS T5  
: 800 N (80 kg)

가

ETIM 5:

ETIM 5.0 Class-ID: EC000127  
ETIM 5.0 :

ETIM 6:

ETIM 6.0 Class-ID: EC000127  
ETIM 6.0 Class :

:

High mechanical load: +65°C  
Low mechanical load: +100°C

가 VAT 가 가 .

(24.04.2024)



## DKK double clamp

		Ø (mm)	x x (mm)	(kg/ )	/ PU
DKK					
52026010	DKK 18	15.0 - 18.0	125.0 x 85.0 x 120.0	2	1
52026012	DKK 26	19.0 - 26.0	125.0 x 85.0 x 120.0	2	1

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02\_03.16