

Crimping Tool PEW TWISTOR

Crimping tool PEW TWISTOR for pressing of (un-)isolated conductor end sleeves with 360° turnable tools surface



360° rotatable crimp insert enables the tool to be adjusted to changing assembly conditions in the best possible way. Properties of crimping pliers with front and side entry combined in one tool. Perfect for tight or changing environments. Side entry ensures an ergonomically optimal crimping process, front entry is particularly suitable for narrow environments and machines. Covers a large cross-section range without adjusting the crimping tool. For end sleeves with a cross-section range of up to 10 mm² or 16 mm², depending on the variant.

For crimping insulated and non-insulated ferrules as well as TWIN ferrules according to DIN 46228. Version "TWISTOR® 16" for square crimping of the ferrules.

Version "TWISTOR® T" for trapezoidal compression of the ferrules.

ETIM 5:	ETIM 5.0 Class-ID: EC000168
	ETIM 5.0 class : , ,
ETIM 6:	ETIM 6.0 Class-ID: EC000168
	ETIM 6.0 Class : / , ,
:	: 16 mm
	:

TWISTOR® is a registered trademark of Rennsteig Werkzeuge GmbH, Germany (GER)

가 VAT 가 가 .

Crimping Tool PEW TWISTOR

	mm ²		(mm)
61814612	0.14 - 16.0		185
61814613	0.14 - 10.0		196

(23.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16

Crimping Tool PEW TWISTOR



(23.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16