

## Tube cable lugs Ni

Tube cable lug made of nickel, heat-resistant up to +650°C, for use with ÖLFLEX® HEAT single cores, available in different dimensions.



가



-



Withstands temperatures up to +650°C.

Compatible with equally heat-resistant ÖLFLEX® HEAT single cores with nickel conductors.

The lowest contact resistances are achieved when contacting with pure nickel conductors.

Suitable for use with KLAUKE crimping tools.

The flat mounting surface and precise processing simplify the crimping process.

For creating a safe crimp connection with multi-wire and fine-wire round cables in classes 2 and 5 in accordance with DIN EN 60228.

ETIM 5:

ETIM 5.0 Class-ID: EC001051

ETIM 5.0 class :

:

Nickel alloy

:

Temperature (max.): +650°C

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02\_03.16



## Tube cable lugs Ni

가 VAT 가 가 .

(24.04.2024)

## Tube cable lugs Ni

	UL	(mm)	d mm
63207020	no	16.5	1.6
63207021	no	17.5	1.6
63207022	no	19	1.6
63207023	no	16.5	2.3
63207024	no	17.4	2.3
63207025	no	19	2.3
63207026	no	22	2.3
63207027	no	22.5	3.6
63207028	no	24	3.6
63207029	no	25	3.6
63207030	no	30.5	3.6
63207031	no	26.5	4.5
63207032	no	28.5	4.5
63207033	no	28.5	5.5
63207034	no	33.5	5.5
63207035	no	37.5	5.5
63207036	no	43	5.5

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02\_03.16