

Tube cable lugs V2A

Tube cable lug made of V2A stainless steel, heat-resistant up to +400°C, for use with ÖLFLEX® HEAT cables/single cores, available in different dimensions.



가

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16

Tube cable lugs V2A



Withstand temperatures up to +400°C.

Compatible with equally heat-resistant ÖLFLEX® HEAT cables/single cores.

Suitable for use with KLAUKE crimping tools.

The flat mounting surface and precise processing simplify the crimping process.

For creating a safe crimp connection with multi-wire and fine-wire round cables in classes 2 and 5 in accordance with DIN EN 60228.

Resistant to corrosion and acid.

ETIM 5:

:

:

,

가

VAT

가

가

.

ETIM 5.0 Class-ID: EC001051

ETIM 5.0 class :

stainless steel V2A

Temperature (max.) +400°C

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16

Tube cable lugs V2A

	UL	(mm)	d mm
63207037	no	17.5	1.6
63207038	no	19	1.6
63207039	no	22	3
63207041	no	22	3
63207042	no	25.5	3
63207043	no	23	4
63207044	no	25	4
63207045	no	26	4
63207046	no	28.5	5
63207047	no	28.5	5
63207048	no	34	6
63207049	no	33.5	6
63207051	no	34	6
63207052	no	37.5	6

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16